SARTURIUS

Product Datasheet

Microsart® Maxi-vac | Microsart® Mini-vac

Laboratory Vacuum Pumps for Microbiology Analysis



Benefits

- Compliance with ISO 8199 "Water Testing Guideline"
- Adjustable vacuum
- Reduced noise
- Structured Membrane Patented protection against leakage
- Compact design Small foot print
- Maintenance-free, 5,000 operating hours guaranteed

Description

Microsart® Maxi-vac and Microsart® Mini-vac are especially designed to meet the requirements of microbiology laboratories. The absolute vacuum is limited to 100 mbar. The adjustable vacuum allows for trouble free working according to ISO 8199 ("Water quality: General guide to enumeration of micro-organisms by culture). The differential pressure during filtration should not exceed 700 mbar to allow a gentle enrichment of the microorganisms.

Efficient Filtration

The intelligent pump design facilitates easy and efficient operation, even in limited working space. The noise development during operation is reduced by 50% compared to conventional membrane pumps. An integral part of the pumps is a newly structured membrane which guarantees leak-proof operation.


The pumps are available in two sizes. The small compact pump Microsart® Mini-vac with 6 L/min air flow is ideal for single vacuum filtrations and the standard pump Microsart® Maxi-vac, with 22 L/min air flow, for 3- to 6-place manifolds.

Specifications

Microsart® Maxi-vac Laboratory Vacuum Pump 22 L, for 3- and 6-place manifolds		
Absolute Vacuum	100 (mbar)	
Noise level [100 mbar]	57.5 - 59.0 dBA	
Operating Pressure (max)	1 (bar)	
Materials (contact with filtrate possible)	Aluminum, CR (Neoprene), NBR (Perbunan)	
Connectors for Tube	ID 9 (mm)	
Ambient Temperature	5 40 °C	
Mains 16694-2-50	230 V 50 Hz	
Mains 16694-1-60	115 V 60 Hz	
Motor Protection	IP 44	
Power P1	130 W	
Operating Current	0.9 A	
Weight	7.1 kg	
Dimensions L×H×W (mm)	261×204×110	

Microsart® Mini-vac Laboratory Vacuum Pump 6 L, for 1-branch manifolds and individual filter holders		
Delivery	6 (L/min)	
Absolute Vacuum	100 (mbar)	
Noise level [100 mbar]	53.5 dBA	
Operating Pressure (max)	2.5 (bar)	
Materials (contact with filtrate possible)	PPS, EPDM, FPM (Fluoroelastomer)	
Connectors for Tube	ID 4 (mm)	
Ambient Temperature	5 40 °C	
Mains 16694-2-50	230 V 50 Hz	
Mains 16694-1-60	115 V 60 Hz	
Motor Protection	IP 20	
Power P1	65 W	
Operating Current	0.63 A	
Weight	1.9 kg	
Dimensions L×H×W (mm)	164×141×90	

Characteristic set-up of a laboratory vacuum filtration



Order Information

Microsart® Maxi-vac Laboratory Vacuum Pump 22 L				
Order Number	Mains	Delivery		
16694-2-50-22	230 V	22 L/min		
16694-1-60-22	115 V	22 L/min		


Microsart® Mini-vac Laboratory Vacuum Pump 6 L			
Mains	Delivery		
230 V	6 L/min		
115 V	6 L/min		
	Mains 230 V		

Spare Parts Microsart® Maxi-vac		
Order Number	Description	
1EV0002	Fine adjustment head incl. vacumeter	
1EH0002	Sound absorber	
1ED0055	Repair part set incl. membrane, sealing ring, valves	

Spare Parts Microsart® Mini-vac		
Order Number	Description	
1EV0001	Fine adjustment head incl. vacumeter	
1EH0001	Sound absorber	
1ED0054	Repair part set incl. membrane, sealing ring, valves	
1EV0003	Fine adjustment head incl. manometer	

Pump capacity at stable vacuum 100 mbar

The graph illustrates the maximum potential of the Laboratory Vacuum pumps during filtration with standard Cellulose Nitrate membranes of different pore sizes. In example, the 6 L vacuum pump delivers enough air flow for three filtrations in parallel with 0.45 µm membranes.



Germany

Sartorius Lab Instruments GmbH & Co. KG Otto-Brenner-Strasse 20 37079 Goettingen Phone +49 551 308 0 USA

Sartorius Corporation 565 Johnson Avenue Bohemia, NY 11716 Phone +1 631 254 4249 Toll-free +1 800 635 2906

For further information, visit www.sartorius.com