SARTURIUS

Minisart® RC Syringe Filters for HPLC Sample Preparation

RC versus PVDF used with Methanol and Acetonitrile


Comparison with PVDF

PVDF is a membrane material often used for HPLC sample preparation. The fluorochemical process needed to produce this raw material can be harmful to the environment. Moreover, PVDF requires an additional coating step with methacrylates to make its membrane surface hydrophilic. In addition, unlike RC syringe filters, those with PVDF membranes are not suitable for DMSO and other amides, or for ketones, esters, and ethers.

Conclusion

Minisart® RC is just as suitable, and often even better, for HPLC sample preparation than PVDF. The broader chemical compatibility of Minisart® RC enables usage with DMSO and for an even wider range of applications.





HPLC Procedure

Column C18: 250×4.6 mm, Flow Rate: 1 mL/min, Wavelength: 210 nm HPLC Injection Volume: 20 μ l, Analysis Time: 65 min, Temperature: 40 °C, Mobile Phases: A) Acetonitrile | B) Water, Gradient: Hold 60% A for 10 min | 60% to 95% A in 20 min | 95% to 100% A in 35 min

Reliable and Ultrapure

Clean & Green

Are you using high-purity filter paper in your lab? Our regenerated cellulose (RC) membrane incorporated in Minisart® RC syringe filters is just as pure, but allpurpose and more convenient.

RC is produced using renewable raw materials in an ecofriendly process, which uses biodegradable components and recycles all solvents employed during manufacture. Our RC polymer is naturally hydrophilic so no additional coating step is necessary. Try our Clean and Green solution to prepare your samples.

Ordering Information

Ømm	Pore Size	Sterile*	Qty Pk	Order No.	
Minisart® RC (F	Regenerated Cellulose + PP)				
25 mm	0.2 μm	Yes	50	17764ACK	
25 mm	0.2 μm	No	50	17764K	
25 mm	0.2 μm	No	200	17764S	
25 mm	0.2 μm	No	500	17764Q	
25 mm	0.45 μm	No	50	17765K	
25 mm	0.45 μm	No	200	17765S	
25 mm	0.45 µm	No	500	17765Q	

\emptyset mm	Pore Size	Sterile*	Qty Pk	Order No.	
15 mm	0.2 μm	Yes	50	17761ACK	
15 mm	0.2 µm	No	50	17761K	
15 mm	0.2 µm	No	500	17761Q	
15 mm	0.45 µm	No	50	17762K	
15 mm	0.45 μm	No	500	17762Q	
4 mm	0.2 µm	No	50	17821K	-
4 mm	0.2 µm	No	500	17821Q	
4 mm	0.45 μm	No	50	17822K	
4 mm	0.45 µm	No	500	17822Q	

^{*} Sterile Minisart® are individually packaged and have been sterilized by ethylene oxide (EO). Not presterilized Minisart® can be sterilized by autoclaving at 121 °C for 30 min | or by using EO.

Would You Like to Use Other Membranes?

Please refer to Minisart® SRP (hydrophobic PTFE for highest chemical compatibility).

Do You Need Minisart® with Pre-filters for Filtration of Highly Particle Laden Samples?

Please refer to Minisart® NY Plus which incorporate a glass fiber pre-filter.

Are You Looking for CE-certified Minisart®?

Please request CE-certified article numbers for Minisart® NML, Minisart® HY and Minisart® SRP. Sartorius offers a full range of syringe filters dedicated for various filtration applications.

Germany

Sartorius Lab Instruments GmbH & Co. KG Otto-Brenner-Strasse 20 37079 Goettingen Phone +49 551 308 0

⊕ For further information, visit

www.sartorius.com

USA

Sartorius Corporation 565 Johnson Avenue Bohemia, NY 11716 Phone +1 631 254 4249 Toll-free +1 800 635 2906